

## Product highlights

- Specifically developed for treatment chairs and are precisely tailored to the specific requirements of hygiene, safety, and maneuverability
- Easy to clean plastic surfaces due to compact design provides hygiene
- Maintenance-free and reliable casters roll smoothly and quietly
- Brake pedals are installed on both sides of underframe providing convenient access with low risk of accidental release and require minimal force for fast locking by foot
- Specifically designed to the requirements of daily use
- Easy-to-understand padlock symbols indicate Locking and Unlocking



Locked  
*all casters fixed*



Unlocked  
*all casters movable*

### Technical data

Diameter of castor	Ø 10 cm
Dynamic load capacity of castors	100 kg each (all together 400 kg)
Material of castor	Polyamid casing, polyurethane tyres (TPU)
Material of brake pedal	high-quality stainless steel
Available for	Comfort-3 Eco/Flex Therapy chairs



Brake pedal  
*on both sides of chassis*

10 cm castor  
*easy & smooth running*

